



d <sub>1</sub>	d <sub>2</sub>	Length l ≈ GN 6335.4														Length l ≈ GN 6335.5						d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>
		Material ST							Material SK							Material ST / SK								
32	M 6	16	20	25	30	35	45	16	20	25	30	35	45	10	16	20	25	30	14	20	10			
40	M 8	16	20	25	30	40	55	15	20	25	30	40	55	20	25	30	40	-	18	25	13			
50	M 10	25	30	35	45	55	-	25	30	35	45	55	-	20	25	30	45	55	22	32	20			
63	M 12	30	35	40	50	60	-	30	35	40	50	60	-	30	40	50	-	-	26	40	25			
80	M 16	-	-	-	-	-	-	30	40	50	60	70	-	-	-	-	-	-	35	50	30			

**Specification**

- **GN 6335.4**
  - Knob  
Technopolymer (Polyamide PA) **ST**  
Shock-resistant, black matte finish
  - Knob  
Duroplast (PF) **SK**  
Black shiny finish
  - Threaded stud  
Steel  
Zinc plated, blue passivated

- **GN 6335.5**
  - Knob  
Technopolymer (Polyamide PA) **ST**  
Shock-resistant, black matte finish  
Threaded stud  
Stainless steel  
M6... M10: AISI 304 Cu  
M12: AISI 303
  - Knob  
Duroplast (PF) **SK**  
Black shiny finish  
Threaded stud  
Stainless steel

- [Plastic Characteristics](#) → Page 2158
- [Stainless Steel Characteristics](#) → Page 2166
- [RoHS](#)

**Information**

Hand knobs GN 6335.4 / GN 6335.5 comply with DIN 6335 type L.

see also...

- [Hand Knobs GN 6335.4 with Loss Protection GN 111.7](#) → Page 2084
- [Hand Knobs GN 6335.5 with Loss Protection GN 111.7](#) → Page 2084

How to order (Threaded stud steel)

**GN 6335.4-SK-80-M16-50**

1 Material

2 d<sub>1</sub>

3 d<sub>2</sub>

4 Length l

How to order (Threaded stud stainless steel)

**GN 6335.5-ST-50-M10-25**

1 Material

2 d<sub>1</sub>

3 d<sub>2</sub>

4 Length l