



STAIN
LESS

d ₁	d ₂	Length l					d ₃	h ₁	h ₂
32	M 6	12	16	20	25	-	12	20	9
40	M 8	20	25	30	40	-	14	25	12
50	M 10	20	25	30	45	55	18	32	15
63	M 12	30	40	50	-	-	20	40	19

Specification

Stainless steel precision casting AISI 316 A4P
Polished

RoHS

Hand knobs GN 6335.5 satisfy the dimensions of the DIN 6335 Type L but differ in terms of their non-scooping geometry, which makes cleaning easier and helps prevent possible build-up of dirt.

They are suitable for areas with special hygiene requirements and, thanks to the material used, for applications in highly corrosive environments.

see also...

	Page
GN 6335.4 Hand Knobs (Plastic, Threaded Stud Steel)	QVX
GN 6335.5 Hand Knobs (Plastic, Threaded Stud Stainless Steel)	QVX
GN 6335.4 Hand Knobs (Cast Iron / Stainless Steel / Aluminum, Threaded Stud Steel)	QVX
GN 6335.5 Hand Knobs (Cast Iron / Stainless Steel / Aluminum, Threaded Stud Stainless Steel)	QVX
GN 6335 Hand Knobs (Stainless Steel Quality Class 4)	QVX

Technical Information

Stainless Steel Characteristics	QVX
---------------------------------	-----

How to order

1	Material
2	d ₁
3	d ₂
4	Length l

GN 6335.5-A4P-40-M8-25

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

