



2		3		4		4										d3	h1	h2
d1	d2	Length l ≈ GN 6336.4						Length l ≈ GN 6336.5										
32	M 6	16	20	25	30	35	45	-	-	-	-	-	-	12	20	9		
40	M 8	16	20	25	30	40	55	20	25	30	40	-	14	25	12			
50	M 10	25	30	35	45	55	-	20	25	30	45	55	18	32	15			
63	M 12	30	35	40	50	60	-	30	40	50	-	-	20	40	19			
80	M 16	30	40	50	60	70	-	-	-	-	-	-	25	50	23			

Specification

- GN 6336.4**
 - Threaded stud
Steel, blackened
 - Knob
Cast iron
Fettled and tumbled

SG
- GN 6336.5**
 - Threaded stud
Stainless steel AISI 303
 - Knob
Stainless steel
precision casting AISI CF-8
Matte shot-blasted
 - Knob
Aluminum, forged
Matte finish (tumbled)
Polished

ES
AM
AP

- The threaded stud is screwed in and secured by a cross-dowel
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

- see also...
- *Star Knobs 6336.4 (Plastic, Threaded Stud Steel)* → Page 545 / 547
 - *Star Knobs 6336.5 (Plastic, Threaded Stud Stainless Steel)*
→ Page 545 / 547
 - *Star Knobs with Threaded Stud GN 5334 / GN 5334.4 (Stainless Steel)*
→ Page 575

How to order (Threaded stud steel)

GN 6336.4-SG-63-M12-50

1	Material
2	d1
3	d2
4	Length l

How to order (Threaded stud stainless steel)

GN 6336.5-AM-40-M8-25

1	Finish (Material)
2	d1
3	d2
4	Length l