



Rost **frei** **Inox** **Stainless** **Steel** **Inch** **sizes** **available**

4 Type

- A** Without bore (unmachined)
- B** With plain through bore H7
- C** With plain blind bore H7
- D** With threaded through bore
- E** With threaded blind bore

2

3

3

d₁			d₂		d₃ H7		d₄	h₁	h₂ min.	h₃	h₄ min.	t₁ min.		t₂
GG	NI	AL	Thread Type D Type E	Bore Type B Type C								Type B, C, D, E	Type B, C, D, E	
32	32	-	M 6	-	B 6	-	12	20	9	21	10	12	12	10
40	40	40	M 8	-	B 8	-	14	25	12	26	13	15	15	13
50	50	50	M 8	M 10	B 8	B 10	18	32	15	34	17	18	18	16
63	63	63	M 10	-	-	-	20	40	19	42	21	22	18	20
63	63	63	M 12	-	B 10	B 12	20	40	19	42	21	22	22	20
80	-	80	M 12	M 16	B 12	B 16	25	50	23	52	25	28	-	20

Specification

- Cast iron **GG**
 - Fettle and tumbled
 - Zinc plated, blue passivated
 - Thread: screw mobility (Type D and E)
- Stainless steel precision casting AISI CF-8 Matte shot-blasted (Type A, D, E) **NI**
- Aluminum Forged (Type A, C, D, E) **AL**
 - Matte finish (ground)
 - Flash mark not visible
 - Polished

• RoHS

On request

- Powder coated

1

5

Information

see also...

- Star Knobs DIN 6336 (Plastic) → Page 544
- Star Knobs GN 6336.1 (Duroplast, with Protruding Steel Bushing) → Page 546
- Star Knobs GN 6336.2 (Technopolymer, with Protruding Steel Bushing) → Page 546
- Star Knobs DIN 6336 with Loss Protection GN 111.7 → Page 2084

How to order (Without bore, matte)

DIN 6336-AL-50-A

- 1** Material
- 2** d₁
- 4** Type

How to order (Cast iron)

DIN 6336-GG-63-M12-D

- 1** Material
- 2** d₁
- 3** d₂ (d₃)
- 4** Type

How to order (Aluminum)

DIN 6336-AL-40-B8-C-PL

- 1** Material
- 2** d₁
- 3** d₃ (d₂)
- 4** Type
- 5** Finish