



3 Type

- E** With threaded blind bore (cover cap)
- D** With threaded through bore

d ₁	d ₂ GN 634			d ₂ GN 634.1			d ₃	d ₄	d ₅	b	h ₁	h ₂	h ₃	h ₄
	M 5	M 6	M 8	M 5	M 6	M 8								
40	M 5	M 6	M 8	M 5	M 6	M 8	13,5	8,5	10	6	20	4	12	18
48	M 5	M 6	M 8	M 6	M 8	-	13,5	8,5	10	7	24	5,5	12	22
55	M 6	M 8	-	M 8	-	-	16	10,5	12	8	28	6,5	18	25
63	M 8	M 10	-	M 10	-	-	19	10,5	14	9	32	7,5	20	29
70	M 8	M 10	-	M 10	-	-	20	13	15	10	36	8	20	32

Specification

- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 130 °C
- Black-gray, similar to RAL 7021, matte

GN 634

Bushing brass

GN 634.1

Bushing stainless steel AISI 303

• Color of the cover cap (matte finish):

- Black-gray, RAL 7021 ● **DSG**
- Orange, RAL 2004 ● **DOR**
- Gray, RAL 7035 ● **DGR**
- Yellow, RAL 1021 ● **DGB**
- Blue, RAL 5024 ● **DBL**
- Red, RAL 3000 ● **DRT**
- Green, RAL 6017 ● **DGN**

• *Plastic Characteristics* → Page 2158

• *Stainless Steel Characteristics* → Page 2166

• **RoHS**

On request

- All in stainless steel



Information

Design and handling of the wing nuts GN 634 / GN 634.1 comply with the requirements and claims of the Ergostyle® product family.

see also...

- *Product Family Ergostyle®* → Page 18
- *Wing Nuts GN 640 (Small Type)* → Page 612
- *Stainless Steel Wing Nuts GN 834* → Page 618
- *Wing Screws GN 633* → Page 608
- *Wing Screws GN 634 / GN 634.1 with Loss Protection GN 111.7*
→ Page 2084

How to order (Bushing brass)

1	d ₁
2	d ₂
3	Type
4	Color of the cover cap

GN 634-55-M8-E-DSG

How to order (Bushing stainless steel)

1	d ₁
2	d ₂
3	Type
4	Color of the cover cap

GN 634.1-55-M8-E-DSG