



ROSTFREI
Inox
Stainless
Steel

² d ₁	³ d ₂ <small>+0,2 +0,4</small>	d ₃	h	For screws with thread	Static load in kN
20	6	16	6	M 6	20
26	8	22	7	M 8	38
28	10	24	8	M 10	40
32	12	28	9	M 12	55

Specification

- Steel **ST**
- Blackened
- Stainless steel AISI 303 **NI**
- Sliding disk
 - Plastic (Polyamide 46)
 - Glass fiber reinforced
 - Temperature resistant up to 120 °C
 - Slightly greased (PTFE-mounting grease)
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

Used in connection with clamping screws, e.g. star knob screws, washers with axial friction bearing GN 6342 offer the following advantages:

- Almost **double** the clamping force owing to lower area friction
- Fixed contact surface acting gently on the element to be clamped

How to order	1 Material
¹ ² ³ GN6342-ST-28-10	2 d ₁
	3 d ₂