



1

2

3

d ₁	d ₂	Length l				d ₃	b	h ₁	h ₂
32	M 4	10	16	-	-	12	6	16,5	3,5
32	M 5	10	16	20	-	12	6	16,5	3,5
32	M 6	10	16	20	25	12	6	16,5	3,5
40	M 8	16	20	25	30	13,5	6,5	21	4,5

Specification

- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 130 °C
- Black, matte finish
- Threaded stud
Steel
Zinc plated, blue passivated
- *Plastic Characteristics* → Page 2158
- RoHS

Information

see also...

- *Wing Screws GN 633* → Page 608
- *Wing Screws GN 531* → Page 615
- *Wing Screws GN 531.1* → Page 617

How to order

GN 639-40-M8-20

1	d ₁
2	d ₂
3	Length l