



ROSTFREI
Inox
Stainless
Steel

1.1

1.2

1.3

1.4

1 2

d ₁	l ₁ ±1							a	b	d ₂	h ₁	h ₂	l ₂	l ₃	t
30	300	350	400	500	600	700	1000	57	38	M 10	60	78	23	12	17

2.1

Specification

3

- Handle tube Ø 30 x 1,5
Aluminum
 - Powder coated
Black, RAL 9005, textured finish ● SW
 - Anodized, natural color ● EL
- Stainless steel AISI 304
Ground, matte shiny finish ● NG
- End pieces plastic
Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 100 °C
 - Black, matte finish
- Threaded bushing
Brass
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

The handle tube of the cabinet U-handles GN 667.2 can be mounted without any further machining, allowing **special lengths** to be realised easily.

2.2

2.3

2.4

How to order

GN 667.2-30-1000-NG

1	d ₁
2	l ₁
3	Finish

