



1

$l_1$	$b_1$	$b_2$	$b_3$	$b_4$	$h_1$	$h_2$	$l_2$	$l_3$	$s$
130	59	31	41	48	29,5	3	100	124	1 ... 5

**Specification**

2

- Plastic Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 110 °C
- Color (matte finish):
  - Black-gray, RAL 7021
  - White, RAL 9002
- Self-tapping screws ISO 7049
  - Steel, zinc plated ST 3,5-20
- *Strength Properties* → Page 2116
- *Plastic Characteristics* → Page 2158
- RoHS



**Information**

The design of the gripping trays GN 739 matches the product family Ergostyle®. These gripping trays are means for opening and closing sliding doors.

The installation opening for the gripping tray must be created according to the dimensions given in the table.

For mounting, the front body is first inserted into the opening of the housing and then the rear body is pushed up from behind to the housing wall. Finally, both parts are screwed together.

see also...

- *Product Family Ergostyle®* → Page 18

How to order	
1	$l_1$
2	Color

**GN 739-130-SG**