



1

l_1	b_1	b_2	b_3	h_1	h_2	l_2	l_3
115	58	31	43,5	19	3	91	94

Specification

2

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 80 °C
- Color (matte finish):
 - Black-gray, RAL 7021
 - White, RAL 9002
- Plastic Characteristics → Page 2158
- RoHS



On request

- In self-extinguishing plastic (SV)

Information

Gripping grips GN 739.1 are useful for opening and closing sliding doors. No mounting screws are required for assembling the recessed grips. The installation opening for the gripping tray must be created according to the dimensions given in the table.

The gripping tray is mounted by first inserting it into the opening on the firmly toothed side and then pressing it in against the opposite side until the locking elements clip into place.

Wall thickness s	$x + 0,2$	$y + 0,2$
0,7 ... 1	51,5	105,3
> 1 ... 1,5	51,7	105,3
> 1,5 ... 2,2	52	105,3

How to order

GN 739.1-115-SG

1 l_1

2 Color

