



3 Type

- D** With internal thread
- E** With threaded stud

1 d_1	2 d_2 Type D	2 d_3 Type E	d_4	h	Length l	t min.
16	M 5	M 6	10	18	10	7
20	M 6	M 8	12	24	12	9
25	M 6	M 8	14	29	14	9
32	M 8	M 10	18	37	16	12
36	M 10	M 12	20	42	18	15

Specification

- **GN 75**
Steel
- Fine turned
- Blackend
- Zinc plated, blue passivated **ZB**
- **GN 75.5**
Stainless steel AISI 304
- Matte shot-blasted **MT**
- Highly polished **PL**
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

On request

- Version in stainless steel (A4 quality)



Information

Mushroom shaped knobs GN 75 / GN 75.5 have a compact and timeless design. Their non-scooping geometry combats dirt build-up and makes cleaning easier.

Mushroom shaped knobs GN 75 in steel are mainly used in mechanical engineering. Mushroom shaped knobs GN 75.5 can be used in aggressive environments thanks to the stainless steel used.

see also...

- *Knobs GN 676.1 (Steel, Blackened)* → Page 88
- *Knobs GN 676.2 (Steel, Zinc Plated)* → Page XYZ
- *Knobs GN 676.5 (Stainless Steel)* → Page 88

How to order (Steel)	1 d_1
1 2 3 GN 75-25-M6-D	2 d_2 (d_3)
	3 Type

Bestellbeispiel (Steel, zinc plated)	1 d_1
1 2 3 4 GN 75-32-M10-E-ZB	2 d_3 (d_2)
	3 Type
	4 Finish

How to order (Stainless steel)	1 d_1
1 2 3 4 GN 75.5-25-M8-E-MT	2 d_3 (d_2)
	3 Type
	4 Finish