



3 Type

- D** With internal thread
- E** With threaded stud

d₁	d₂ Type D	d₃ Type E	d₄	d₅	h	Length l	t min.
20	M 5	M 5	14	14,8	24	10	7
25	M 6	M 6	16	16,8	29	12	9
32	M 8	M 8	18	18,8	37	14	12

Specification

- Stainless steel AISI 316L
 - Matte finish (Ra < 0.8 µm) **MT**
 - Polished finish (Ra < 0.8 µm) **PL**
- Sealing ring
 - H-NBR **H**
Temperature resistant -25 °C to +150 °C
 - EPDM **E**
Temperature resistant -40 °C to +120 °C
 - Blue
 - Hardness 85 ±5 Shore A
 - FDA compliant
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

Accessory

- Sealing Rings GN 7600 → Page 1596

On request

- with FKM sealing ring (Fluorine rubber) **F**

Information

Mushroom shaped knobs GN 75.6 are intended for use in hygienic areas. The sealed mounting surface enables mounting without dead spaces; the impervious geometry in combination with the high quality finish prevents the accumulation of dirt and facilitates cleaning.

They have a compact and timeless design.

see also...

- *Product Family Hygienic Design* → Page 16

How to order

1	d₁
2	d₃ (d₂)
3	Type
4	Finish
5	Material (Sealing ring)

GN 75.6-25-M6-E-MT-H