



- 2 Type**
- D** Fixing with slotted holes
  - E** Fixing with bores

1		1	
d Bore		For tube outside Ø	
Type D	Type E		Standard description in inch
B 42,4	-	42,4	1 1/4"
B 48,3	B 48,3	48,3	1 1/2"
B 60,3	-	60,3	2"

**Specification**

- Plastic (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 100 °C
  - Black, matte finish
- Hexagon screws DIN 931  
Stainless steel AISI 304
- Hexagon nuts DIN 934  
Stainless steel AISI 304
- Washers  
Stainless steel AISI 304
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**On request**

- Type D with square 45 x 45

**Information**

- see also...
- *Base Plate Connector Clamps GN 163 (Aluminum)* → Page 1733
  - *Construction Tubes GN 990* → Page 1835

<b>How to order</b>	1	d
	2	Type
<b>GN86-B48,3-E</b>		