



Swing clamp GN 876



For swing clamps Size	² d ₁	³ m	d ₂	h	Length l
25	M 40x1,5	37	5,4	9	50
32	M 50x1,5	45	6,6	12	60
40	M 55x1,5	50	6,6	12	65
50	M 65x1,5	58	9	15	75
63	M 80x1,5	70	9	15	88

Specification

- Steel
- Zinc plated, blue passivated
- RoHS

¹ **ST**

Information

Threaded flanges GN 876.1 designed as accessories to swing clamps GN 876.

This makes it unnecessary to tap the mounting hole of the part.

see also...

- *Swing Clamps GN 876 (with Screw-In Thread)* → Page 844
- *Slotted Locknuts DIN 70852* → Page 1075

How to order

GN 876.1-ST-M55x1,5-50

¹	Material
²	d ₁
³	m

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

