



Mounting example



1 2

b Size of the slide	l ₁	d for socket cap screws DIN 912	h ₁	h ₂	l ₂	l ₃	l ₄	l ₅
30	41	M 2,5	8,4	4,2	35,4	41	35,4	6,5
50	67	M 3	14	7	58	67	58	10
80	105	M 4	25	12,5	92	105	92	14,5
120	145	M 5	27,6	13,8	131,8	145	131,8	14,5

Specification

- Aluminum
Anodized, natural color
- Socket cap screws DIN 912
Stainless steel
- RoHS

Information

With connecting sets GN 900.2 two adjustable slide units GN 900 can be combined to produce an X-Y axis configuration.

This combination is achieved with a clamping system which eliminates the use of any kind of fixing holes in the slide.

The stationary base of the second adjustable slide unit is clamped on to the side of the first unit to give the X-Y configuration. The slides on both units together give the X-Y movement.

The small fixing plate serves for the 90° alignment and fine adjustment of the X-Y axis configuration.

All parts required to make up a set are included.

see also...

- *Adjustable Slide Units GN 900* → Page 1938

How to order

GN 900.2-50-67

- 1 b
- 2 l₁

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

