



1	2	3					d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub> ≈
l <sub>1</sub>	d <sub>1</sub>	l <sub>2</sub>							
45	M 6	20	-	-	-	-	10	9	34
63	M 6	20	-	-	-	-	10	12	44
63	M 8	25	30	35	40	50	13	12,5	42
78	M 8	25	30	35	40	50	13	15	52
78	M 10	35	50	55	60	65	16	16	50
92	M 10	35	50	55	60	65	16	16	60

**Specification**

- Handle  
Zinc die casting  
Powder coated  
Silver, RAL 9006, textured finish ● SR
- Threaded insert and retaining screw  
Stainless steel AISI 303
- *Stainless Steel Characteristics* → Page 2166
- RoHS



**Information**

Adjustable hand levers GN 911 replace the socket cap screws DIN 912 of the tube clamp connectors and linear actuator connectors.

The table of dimensions of the tube clamp connectors and linear actuator connectors shows the matching hand lever for each screw location.

How to order

1 2 3 4  
**GN 911-63-M8-30-SR**

1	l <sub>1</sub>
2	d <sub>1</sub>
3	l <sub>2</sub>
4	Color