



3.1

3.2

3.3

3.4

1

2

3

l_1	d_1	l_2	d_2	h_1	$h_2 \approx$
44	M 6	20	10	8,5	32
63	M 6	20	10	9	40
63	M 8	25	13	13,5	44
78	M 8	25	13	14,5	52

3.5

3.6

Specification

4

- Handle
Plastic Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 130 °C
- Black-gray, RAL 7021, matte finish ● **SG**
- Serrated ring
Zinc die casting
- Threaded insert and retaining screw
Stainless steel AISI 303
- *Plastic Characteristics* → Page XYZ
- *Stainless Steel Characteristics* → Page XYZ
- RoHS

Information

For plastic clamp connectors, adjustable hand levers GN 911.9 replace the hexagon socket cap screws DIN 912, the clamping point or the joint axis. There are two handle lengths to choose from, depending on the thread size.

3.7

3.8

3.9

How to order		1	l_1
		2	d_1
		3	l_2
		4	Color
GN 911.9-63-M8-25-SG			

