



1			2					
l_1			d_1	d_2	d_3	h_1	$h_2 \approx$	$l_2 \approx$
GN 99.5	GN 99.6 AISI 304	GN 99.6 AISI 316L						
63	63	63	M 8	16	10	12,5	30,5	60
80	80	80	M 10	20	12	15	37	76
100	100	100	M 12	25	14	19	46	95
125	125	-	M 16	32	18	25	58,5	119
160	160	-	M 20	40	20	31	73	152

Specification

GN 99.5		
Steel	—	
Zinc plated, blue passivated	—	
GN 99.6		
• Stainless steel AISI 304		
• Stainless steel AISI 316L		A4
• Matte shot-blasted		
Shaft		
Butt-welded		
RoHS		



see also...

	Page
DIN 99 Stainless Steel Clamping Levers (Steel / Stainless Steel)	QVX
GN 206 Stainless Steel Clamp Nuts (Cast Iron / Stainless Steel Precision Casting)	QVX

Technical Information

Stainless Steel Characteristics	QVX
---------------------------------	-----

How to order (Steel)

GN 99.5-100-M12

1	l_1
2	d_1

How to order (Stainless Steel AISI 304)

GN 99.6-100-M12

1	l_1
2	d_1

How to order (Stainless Steel AISI 316L)

GN 99.6-80-M10-A4

1	l_1
2	d_1
3	Material

