



1

2

l_1	GN 99.5	GN 99.6 AISI 304	GN 99.6 AISI 316L (A4)	d_1	d_2	d_3	h_1	$h_2 \approx$	$l_2 \approx$
63	63	63	63	M 8	16	10	12,5	30,5	60
80	80	80	80	M 10	20	12	15	37	76
100	100	100	100	M 12	25	14	19	46	95
125	125	-	-	M 16	32	18	25	58,5	119
160	160	-	-	M 20	40	20	31	73	152

Specification

- GN 99.5**
Steel —
Zinc plated, blue passivated
- GN 99.6**
Stainless steel —
- AISI 304 —
- AISI 316L **A4**
- Matte shot-blasted
- Shaft butt-welded
- Stainless Steel Characteristics → Page 2166
- RoHS

3

Information

- see also...
- Clamping Levers DIN 99 (Steel, Blackened) → Page 502
 - Stainless Steel Clamping Levers DIN 99 (Steel, Matte Shot-Blasted) → Page 502
 - Clamp Nuts GN 206 (Cast Iron) → Page 508
 - Stainless Steel Clamp Nuts GN 206 → Page 508

How to order (Steel)

GN 99.5-100-M12

1 l_1
2 d_1

How to order (Stainless steel, AISI 304)

GN 99.6-80-M10

1 l_1
2 d_1

How to order (Stainless steel, AISI 316L)

GN 99.6-80-M10-A4

1 l_1
2 d_1
3 Material