Standard parts in this product family are compatible with Aluminum profiles from the i and b modular systems (Page 1744), as well as with common Aluminum profile systems from other manufacturers. Using slot nuts (Page 1748 / 1776) or hammerhead screws (Page 1779) or nuts (Page 1778), Ganter standard elements can be easily and cost-effectively mounted in the groove of the profiles.

- for groove widths 6, 8 and 10 mm
- for grid size 30, 40 and 45 mm

GN 565.1
Cabinet U-Handles
Aluminum,
Mounting from
the Operator's Side
Page 89

GN 565.2
Inclined
Cabinet U-Handles
Aluminum
Page 96

GN 630.1
Cabinet U-Handles
Plastic
ganternorm.com

GN 528
Cabinet U-Handles
Plastic
Page 100

GN 728
Cabinet U-Handles
Aluminum
Page 104

GN 728.5
Cabinet U-Handles
Stainless Steel
Page 104

GN 628
Cabinet U-Handles
Plastic
Page 113

GN 629
Cabinet U-Handles
Plastic,
with Cover Cap
Page 122

GN 629.1
Cabinet U-Handles
Plastic
Page 122

GN 181
Fastening Sets
Zinc Die Casting,
for Mounting
Cabinet U-Handles
Page 140

GN 328
Cabinet U-Handles
Aluminum
Page 142

GN 328.5
Cabinet U-Handles
Stainless Steel
Precision Casting
Page 142

GN 333.1
Tube Handles
Tube Aluminum,
Legs Zinc Die Casting
Page 158

GN 333
Tube Handles
Tube Aluminum,
Legs Zinc Die Casting
Page 164

GN 667
Cabinet U-Handles
Aluminum,
End Pieces Plastic
Page 166

GN 667
Cabinet U-Handles
Stainless Steel,
End Pieces Plastic
Page 166

GN 334.1
Oval Tubular Handles
Tube Aluminum,
Legs Zinc Die Casting
Page 168

GN 335
Oval Tubular Handles
Tube Aluminum,
Legs Zinc Die Casting
ganternorm.com

GN 630
Ledge Handles
Plastic
ganternorm.com

GN 412
Indexing Plungers
Zinc Die Casting,
with Flange for Mounting,
with / without Rest Position
Page 884

GN 416
Spring Latch
Guide Zinc Die Casting,
Plunger Pin Steel,
with Flange for Mounting
Page 885

GN 416.1
Locators
for Spring Latch GN 416,
Zinc Die Casting
Page 886

GN 417.1
Locators
for Indexing Plungers,
Steel / Stainless Steel
Precision Casting
Page 887

GN 417
Indexing Plungers
Zinc Die Casting,
with Lifting Ring / Wire Loop,
without Rest Position
Page 888

GN 417
Indexing Plungers
Stainless Steel
Precision Casting,
with Lifting Ring / Wire Loop,
without Rest Position
Page 888

GN 417
Indexing Plungers
Steel,
with knob,
with / without
Rest Position
Page 889

GN 417
Indexing Plungers
Stainless Steel,
with knob,
with / without
Rest Position
Page 889

GN 722.6
Indexing Plungers
Steel,
with Flange for Mounting,
without Rest Position
Page 890

GN 722.6
Indexing Plungers
Stainless Steel,
with Flange for Mounting,
without Rest Position
Page 890

GN 722.6
Indexing Plungers
Steel,
with Flange for Mounting,
with Rest Position
Page 891

GN 722.6
Indexing Plungers
Stainless Steel,
with Flange for Mounting,
with Rest Position
Page 891

GN 722.6
Indexing Plungers
Steel,
with Flange for Mounting,
with Rest Position / Latch
Page 892

GN 722.6
Indexing Plungers
Stainless Steel,
with Flange for Mounting,
with Rest Position / Latch
Page 892

GN 724.6
Indexing Plungers
Steel / Stainless Steel,
with Chamfered Pin,
with Flange for Mounting
Page 894

GN 412.1
Mounting blocks
Zinc Die Casting,
for Indexing Plungers /
Cam Action
indexing Plungers
Page 914

GN 612.2
Cam Action
Indexing Plungers
Steel,
with Flange for Mounting
Page 926

GN 612.9
Cam Action Indexing Plungers
Zinc Die Casting,
with Flange for Mounting
Page 927

GN 722.3
Spring Latches
Steel,
with Flange for Mounting
Page 928

GN 722.3
Spring Latches
Stainless Steel,
with Flange for Mounting
Page 928

GN 724.3
Spring Latches
Steel / Stainless Steel,
with Chamfered Pin,
with Flange for Mounting
Page 930

GN 3492
Mounting Blocks
Stainless Steel
Page 973

GN 1050
Quick Release Couplings
Housing Aluminum
Page 1118

GN 1050.1
Studs
for Quick Release
Couplings GN 1050,
Steel
Page 1120

GN 1050.2
Flanges
for Quick Release
Couplings GN 1050,
Steel
Page 1121

GN 449.1
Spring-Bolt Door Latches
Plastic, Adjustable,
with/without
Finger Handle
ganternorm.com

GN 449.4
Snap Latches
Plastic,
with Gripping Tray
Page 1248

GN 936
Slam Latches
Zinc Die Casting,
with/without Lock
Page 1250

GN 4490
Ball Catches
Zinc Die Casting
Page 1252

GN 4490
Ball Catches
Stainless Steel
Page 1252

GN 4490.1
Mounting Plates
Stainless Steel,
for GN 4490
ganternorm.com

GN 4490.2
Mounting Plates
Stainless Steel,
for GN 4490
ganternorm.com

GN 702
Stop Locks
Zinc Die Casting,
with 4 Indexing Positions
Page 1256

GN 938
Hinges
Zinc Die Casting,
for Panels
Page 1304

GN 2295
Hinges
Aluminum,
Three-Part
Page 1322

GN 2295
Hinges
Aluminum,
Three-Part,
Vertically Elongated
Page 1323

GN 2291
Hinge leafs
Aluminum,
with / wihout Guide Step
ganternorm.com

GN 159
Hinges
Plastic
Page 1324

GN 159.1
Doppel-Hinges
Plastic
ganternorm.com

GN 161
Hinges
Zinc Die Casting
ganternorm.com

GN 127
Hinges
Zinc Die Casting,
Adjustable
Page 1368

GN 127
Hinges
Stainless Steel,
Adjustable
Page 1368

GN 236
Hinges
Plastic,
Adjustable
Page 1369

GN 151.4
Hinges
Plastic,
Adjustable
by Slotted Holes
ganternorm.com

GN 2292
Hinges
Aluminum,
with / wihout Guide Step
Detachable
ganternorm.com

GN 2294
Hinges
Aluminum,
Detachable
ganternorm.com

GN 139.1
Hinges
with Safety Switch
Zinc Die Casting
Page 1390

GN 139.2
Hinges
Zinc Die Casting,
without Switch
Page 1390

GN 139.3
Mounting Plates
Steel,
for Hinges
GN 139.1 / GN 139.2
ganternorm.com

GN 139.4
Mounting Plates
Zinc Die Casting,
for Hinges
GN 139.1 / GN 139.2
ganternorm.com

GN 239.6
Hinges
with Safety Switch
Plastic
Page 1394

GN 239.7
Hinges
Plastic,
without Switch
Page 1394

GN 239.8
Mounting Plates
Plastic,
for Hnges
GN 239.6 / GN 239.7
ganternorm.com

GN 239.4
Hinges
with Switch
Plastic
Page 1396

GN 239.3
Hinges
Plastic,
without Switch
Page 1396

GN 145
Flanged
Connector Clamps
Aluminum
Page 1814

GN 145
Flanged
Connector Clamps
Stainless Steel
Page 1814



GN 146.3
Flanged Connector Clamps
Aluminum
Page 1815

GN 146.9
Flanged Connector Clamps
Plastic
Page 1817

GN 162.3
Base Plate Connector Clamps
Aluminum / Stainless Steel
Page 1820

GN 231
Tube Supports
Aluminum
Page 1830

GN 271
Swivel Clamp Connector Bases
Aluminum
Page 1834

GN 271
Swivel Clamp Connector Bases
Stainless Steel
Page 1834

GN 281
Swivel Clamp Connector Joints
Aluminum / Stainless Steel
Page 1838

GN 271.4
Sensor Holders
Aluminum
ganternorm.com

GN 473
Base Plate Mounting Clamps
Aluminum
Page 1860

GN 175
Base Plate Mounting Clamps
Plastic
Page 1861

GN 477
Mounting Clamps
Aluminum
Page 1862

GN 480
Flanged Mounting Bolts
Steel
Page 1876



GN 485
Base Plate Swivel Mounting Clamps
Aluminum
Page 1877

GN 967
Angle Pieces, Shackles
Steelblech,
for Profile Systems
Page 1886

GN 3490
Threaded Flanges
Steel Precision Casting,
for Profile Systems
Page 1887

GN 939
Panel Support Clamps
Zinc Die Casting
Page 1888

GN 938.1
T-Nuts
Zinc Die Casting,
for GN 938 / GN 939
Page 1891

GN 649
Panel Support Clamps
Plastic
Page 1892

GN 4470
Magnetic Catches
with Rubberized Magnetic Surface
Page 2244

GN 56
Retaining Magnets
Housing plastic
ganternorm.com