

GN 62444 Cable Glands, Metric Thread				
Article no.	Approvals			
	UL	VDE	CSA	DNV
62444-M12x1,5-6-MS	cURus	VDE	see UL	DNV
62444-M16x1,5-8-MS	cURus	VDE	see UL	DNV
62444-M16x1,5-10-MS	cURus	VDE	see UL	DNV
62444-M20x1,5-12-MS	cULus	VDE	see UL	DNV
62444-M25x1,5-14-MS	cULus	VDE	see UL	DNV
62444-M25x1,5-17-MS	cULus	VDE	see UL	DNV
62444-M32x1,5-18-MS	cULus	VDE	see UL	DNV
62444-M32x1,5-21-MS	cULus	VDE	see UL	DNV
62444-M40x1,5-25-MS	cULus	VDE	see UL	DNV
62444-M50x1,5-32-MS	cULus	VDE	see UL	DNV
62444-M50x1,5-38-MS	cULus	VDE	see UL	DNV
62444-M63x1,5-44-MS	cULus	VDE	see UL	DNV
62444-M12x1,5-6-NI	cURus	VDE	see UL	DNV
62444-M16x1,5-8-NI	cURus	VDE	see UL	DNV
62444-M16x1,5-10-NI	cURus	VDE	see UL	DNV
62444-M20x1,5-12-NI	cULus	VDE	see UL	DNV
62444-M25x1,5-14-NI	cULus	VDE	see UL	DNV
62444-M25x1,5-17-NI	cULus	VDE	see UL	DNV
62444-M32x1,5-18-NI	cULus	VDE	see UL	DNV
62444-M32x1,5-21-NI	cULus	VDE	see UL	DNV
62444-M40x1,5-25-NI	cULus	VDE	see UL	DNV
62444-M40x1,5-28-NI	cULus	VDE	see UL	DNV
62444-M50x1,5-32-NI	cULus	VDE	see UL	DNV
62444-M50x1,5-38-NI	cULus	VDE	see UL	DNV
62444-M63x1,5-44-NI	cULus	VDE	see UL	DNV
62444-M12x1,5-6-KLG	cURus	VDE	cCSAus	DNV
62444-M16x1,5-8-KLG	cURus	VDE	see UL	DNV
62444-M16x1,5-10-KLG	cURus	VDE	cCSAus	DNV
62444-M20x1,5-12-KLG	cULus	VDE	cCSAus	DNV
62444-M20x1,5-14-KLG	cULus	VDE	cCSAus	DNV
62444-M25x1,5-17-KLG	cULus	VDE	cCSAus	DNV
62444-M25x1,5-18-KLG	cULus	VDE	cCSAus	DNV
62444-M32x1,5-21-KLG	cULus	VDE	cCSAus	DNV
62444-M32x1,5-25-KLG	cULus	VDE	cCSAus	DNV
62444-M40x1,5-28-KLG	cULus	VDE	cCSAus	DNV
62444-M40x1,5-32-KLG	cULus	VDE	cCSAus	DNV
62444-M50x1,5-38-KLG	cULus	VDE	cCSAus	DNV
62444-M63x1,5-44-KLG	cULus	VDE	cCSAus	DNV



GN 62444 Cable Glands, PG Thread

Article no.	Approvals UL	VDE	CSA	DNV
62444-PG7-6-MS	cURus	-	see UL	DNV
62444-PG9-8-MS	cURus	-	see UL	DNV
62444-PG11-10-MS	cURus	-	see UL	DNV
62444-PG13,5-12-MS	cULus	-	see UL	DNV
62444-PG16-14-MS	cULus	-	see UL	DNV
62444-PG21-18-MS	cULus	-	see UL	DNV
62444-PG29-25-MS	cULus	-	see UL	DNV
62444-PG36-32-MS	cULus	-	see UL	DNV
62444-PG48-44-MS	cULus	-	see UL	DNV
62444-PG7-6-NI	cURus	-	see UL	DNV
62444-PG9-8-NI	cURus	-	see UL	DNV
62444-PG11-10-NI	cURus	-	see UL	DNV
62444-PG13,5-12-NI	cULus	-	see UL	DNV
62444-PG16-14-NI	cULus	-	see UL	DNV
62444-PG29-25-NI	cULus	-	see UL	DNV
62444-PG36-32-NI	cULus	-	see UL	DNV
62444-PG48-44-NI	cULus	-	see UL	DNV
62444-PG7-6-KLG	cURus	-	cCSAus	DNV
62444-PG9-8-KLG	cURus	-	cCSAus	DNV
62444-PG11-10-KLG	cURus	-	cCSAus	DNV
62444-PG13,5-12-KLG	cULus	-	cCSAus	DNV
62444-PG16-14-KLG	cULus	-	cCSAus	DNV
62444-PG29-25-KLG	cULus	-	cCSAus	DNV
62444-PG36-32-KLG	cULus	-	cCSAus	DNV
62444-PG42-38-KLG	cULus	-	cCSAus	DNV
62444-PG48-44-KLG	cULus	-	cCSAus	DNV

GN 62444 Cable Glands, NPT Thread

Article no.	Approvals UL	VDE	CSA	DNV
62444-NPT3/8-8-MS	cURus	-	see UL	DNV
62444-NPT1/2-12-MS	cULus	-	see UL	DNV
62444-NPT1/2-14-MS	cULus	-	see UL	DNV
62444-NPT3/4-18-MS	cULus	-	see UL	DNV
62444-NPT3/8-10-KLG	cULus	-	cCSAus	DNV
62444-NPT1/2-12-KLG	cULus	-	cCSAus	DNV
62444-NPT1/2-14-KLG	cULus	-	cCSAus	DNV
62444-NPT3/4-18-KLG	cULus	-	cCSAus	DNV
62444-NPT1-25-KLG	cULus	-	cCSAus	DNV