




Original design CWN./CWN.FP

 **Form**

- E mit Gewinde-Sackloch
D mit Gewinde-Durchloch

1

2

d ₁	d ₂		d ₃	d ₄	b	h ₁	h ₂	t ₁ min.	t ₂
	Form E	Form D							
32	M 4	-	12	8	6	16,5	3,5	6	-
32	M 5	M 5	12	8	6	16,5	3,5	6	12
32	M 6	M 6	12	8	6	16,5	3,5	8	12
40	M 6	-	13,5	9,5	6,5	21	4,5	12	-
40	M 8	M 8	13,5	9,5	6,5	21	4,5	13	16

Ausführung

- Kunststoff
Thermoplast (Polyamid PA)
- glasfaserverstärkt
- temperaturbeständig bis 130 °C
- schwarz, matt
- Buchse
Messing
- *Kunststoff-Eigenschaften* → Seite 2158
- RoHS

Hinweis

siehe auch...

- *Flügelmuttern GN 634* → Seite 606
- *Flügelmuttern GN 532* → Seite 614
- *Flügelmuttern GN 532.1* → Seite 616

Bestellbeispiel


GN 640-32-M6-E
1 d₁2 d₂

3 Form