



**Rost frei** Inox  
Stainless  
Steel

**1 Type**  
**SC** With key  
(same lock)

**2**

Latch distance <b>A</b>													<b>d</b>	<b>h</b>	
6	10	14	18	20	22	24	26	28	30	34	38	40	50	28	4

**Specification**

- Lock housing  
Stainless steel AISI 303 **NI**
- Latch arm  
Stainless steel AISI 304
- Key  
Nickel silver with plastic hand piece
- Other parts  
Stainless steel AISI 304
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

**Accessories**

- Protective Caps GN 120 → Page 1268
- Opening Handles GN 120.1 → Page 1269
- Protective Guide Plates GN 120.2  
→ Page 1270

**On request**

- Lock with Different Combinations

**3**

**Information**

The lockable stainless steel latches GN 115 lock by a turning operation limited to 90° which moves the locking behind the door frame. The bevels of the locking ease the closing of the door. Thanks to the stainless steel materials used, the latches are optimally suited for use in corrosive environments.

Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 50 mm.

The latches are delivered with 2 keys and loosely enclosed latch arm. The key can be removed in both end positions. The lock is standard, so that every lock can be opened with the same key.

see also...

- *Construction and Assembly Instructions* → Page 1201
- *List of Latch Types* → Page 1196 ff.
- *Stainless Steel Latches GN 115 (Operation with Socket Keys)*  
→ Page 1202
- *Stainless Steel Latches GN 115 (with Operating Elements)* → Page 1200

**How to order**

**GN 115-SC-40-NI**

<b>1</b>	<b>Type</b>
<b>2</b>	<b>Latch distance A</b>
<b>3</b>	<b>Material</b>