



**1 Type**  
VH8 With square spindle

**2**

Latch arm distance **A**

6	10	14	18	20	22	24	26	28	30	34	38	40	50
---	----	----	----	----	----	----	----	----	----	----	----	----	----

**Specification**

- Lock housing / Square spindle  
Stainless steel AISI 316Ti **NI**
- Latch arm  
Stainless steel AISI 304
- Hexagon screw  
Stainless steel AISI 304
- Fixing nut  
Stainless steel AISI 304
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**Accessory**

- Socket Keys 119.2 → Page 1266

**3**

**Information**

Stainless steel hygienic latches GN 115 meet the requirements for a hygienic design according to DIN 1672-2 and DIN 14159.

Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 28 mm.

The latches are supplied with loosely enclosed latch arm.

see also...

- *Construction and Assembly Instructions* → Page 1201
- *List of Latch Types* → Page 1196 ff.
- *Stainless Steel Latches GN 115 (Operation with Socket Keys)* → Page 1202
- *Stainless Steel Latches GN 115 (with Operating Elements)* → Page 1206

**How to order**

**GN 115-VH8-20-NI**

<b>1</b>	Type
<b>2</b>	Latch arm distance A
<b>3</b>	Material