



**elisa**  
Original design VCK.

### 3 Type

- R Clamping direction right turn
- L Clamping direction left turn

1

2

| d <sub>1</sub> | Length l |    |    | d <sub>2</sub> | d <sub>3</sub> | d <sub>4</sub> | h <sub>1</sub> | h <sub>2</sub> |
|----------------|----------|----|----|----------------|----------------|----------------|----------------|----------------|
| 50             | 24       | 46 | -  | 14             | 12             | 45             | 12             | 33             |
| 60             | 46       | 54 | 64 | 14             | 12             | 45             | 12             | 37             |
| 70             | 54       | 64 | -  | 14             | 12             | 45             | 12             | 44             |

## Specification

- Star knob GN 5337  
Plastic Duroplast (PF)
  - Black, shiny finish
  - Temperature resistant up to 110 °C
- Bolt  
Steel  
Zinc plated, blue passivated
- Cam latch  
Steel, sintered  
Predrilled hole for pinning
- Clamping pin (for cam latch)  
Steel  
Blackened  
Ø 3 x 20 mm DIN 1481
- *Plastic Characteristics* → Page 2158
- RoHS

## On request

- Stainless steel version

## Information

Latches GN 118 have a pulling-in range of 2 mm.

They are available as a left and a right version, depending on whether the locking action is left or right.

see also...

- *List of Latch Types* → Page 1196 ff.
- *Latches GN 119* → Page 1240
- *Latches GN 117* → Page 1238

How to order

GN 118-50-46-R

|   |                |
|---|----------------|
| 1 | d <sub>1</sub> |
| 2 | Length l       |
| 3 | Type           |