



ROSTFREI  
Inox  
Stainless  
Steel

**4 Type**  
**B With through-holes**

3.1

3.2

3.3

3.4

3.5

**2** **2** **2** **3**

$l_1$	$l_3$	$l_4$	$l_2$	$d_1$	$d_2$	$h$	$l_5$	$l_6$	$m_1$	$m_2$	$m_3$	$s$
70	105	140	50	6	6,5	12	35	70	42	30	39	3

3.6

**Specification**

**1** **5**

- Stainless steel **NI**
- AISI 304
- Plain **BL**
- Pin
- Stainless steel AISI 304
- Riveted
- Load Rating Information → Page 2121
- Stainless Steel Characteristics → Page 2166
- RoHS

**On request**

- Without bores
- With countersunk holes
- Other surface types

**Information**

Pointed stainless steel sheet metal hinges GN 1364 are characterized by their compact and universal dimensioning as well as their attractively shaped design. The materials used also permit applications in aggressive environments.

Type B is fastened via the existing through-holes using screws or rivets.

see also...

- List of Hinge Types → Page 1284 ff.
- Sheet Metal Hinges GN 136 (Steel / Stainless Steel) → Page 1300

3.7

3.8

3.9

How to order

<b>1</b>	Material
<b>2</b>	$l_1$ ( $l_3, l_4$ )
<b>3</b>	$l_2$
<b>4</b>	Type
<b>5</b>	Finish

**GN 1364-NI-70-50-B-BL**