



ROSTFREI
Inox
Stainless
Steel

4 Type

- A** Without bores (only in stainless steel NI)
- B** With through-holes
- C** With countersunk holes

2

3

l_1	l_2 Square 1,5x elongated	d_1	d_2	d_3	d_4	m_1	m_2	m_3	s	
30	30	45	3	3,2	4	6,4	18	18	16,5	1,5
40	40	60	4	4,2	5	8,3	25	25	22,5	2
50	50	75	6	5,2	5	8,3	30	30	27,5	2
60	60	90	6	5,2	5	8,3	36	36	33	2

Specification

- Steel **ST**
 - Only type B and C
 - Zinc plated, blue passivated
- Stainless steel AISI 304 **NI**
All types
- Pin
 - Stainless steel AISI 304
 - Riveted
- *Load Rating Information* → Page 2121
- *Stainless Steel Characteristics* → Page 2166
- RoHS

1

Information

Sheet metal hinges GN 136 are available in many different versions and are suitable for light to medium-duty applications.

Type A can be fixed in place by welding or by using holes made by the customer.

see also...

- *List of Hinge Types* → Page 1284 ff.
- *Stainless Steel Sheet Metal Hinges GN 1362 (for Welding)* → Page 1302
- *Stainless Steel Sheet Metal Hinges GN 1364 (Pointed)* → Page 1303
- *Hinges GN 1366 (Steel Profile, for Welding)* → Page 1304

How to order

GN 136-NI-40-40-A

- 1** Material
- 2** l_1
- 3** l_2
- 4** Type