


elesa
Original design CFA/SL




- 3 Type**
- H** Vertically adjustable
 - B** Horizontally adjustable
 - HB** Vertically and horizontally adjustable


Type H



Type B



Type HB



1

2

l_1	l_2	d_1	d_2	h_1	h_2	h_3	h_4	l_3	m_1	m_2	t
64	65	6,5	5	23	13,5	15	30	24	40	40	6,5

Specification

- Plastic (Polyamide PA)
 - Black, matte finish
 - Temperature resistant up to 80 °C
- Pin
Stainless steel AISI 303
- *Load Rating Information* → Page 2126
- *Plastic Characteristics* → Page 2158
- **RoHS**

Information

see also...

- *Product Family Standard Parts for Profile Systems* → Page 1377
- *List of Hinge Types* → Page 1284 ff.
- *Hinges GN 238 (Adjustable, Zinc Die Casting)* → Page 1372
- *Hinges GN 127 (Adjustable, Zinc Die Casting)* → Page 1375
- *Hinge GN 236 (Adjustable, Plastic)* → Page 1376
- *Assembly Sets for Profile Systems 30 / 40 GN 965* → Page 2086
- *Assembly Sets for Profile Systems 30 / 40 / 45 GN 968* → Page 2096

How to order

GN 151.4-64-65-HB

- 1** l_1
- 2** l_2
- 3** Type

