



EDELSTAHL®
Rostfrei
Inox
Stainless
Steel

3.1

3.2

3.3

3.4



d	Max. spring load in N ≈	For serrated locking plates GN 187.4 / GN 189 - d ₀	For locking plates GN 187.5 - d ₀
15	20	22	-
18	35	27	27
23	55	32	32
29	45	40	40

3.5

3.6

Specification

- Stainless steel AISI 301
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Thrust springs GN 187.2 are installed between the serrated locking plates GN 187.4 or GN 189 and locking plates GN 187.5 and ensure secure separation of the serrated locking plates when removed.

see also...

- *Serrated Locking Plates (Steel / Stainless Steel) GN 187.4* → Page 1100
- *Serrated Locking Plates GN 189 (Plastic)* → Page 1107
- *Locking Plates GN 187.5 (Stainless Steel)* → Page 1104

3.7

3.8

3.9

How to order

GN 187.2-18

1 d

