



**Rostfrei**  
Inox  
Stainless  
Steel

- 3 Identification no.**
- 2** With 2 stainless steel socket cap screws DIN 912

Adjustable hand lever  
GN 911 / GN 911.3

| <b>1</b> $d_1$ Bore |                 | <b>2</b> $d_2$ Bore |                 | <b>k</b> Clamping length | $l_1$ | $l_2$ | $m$ | $z_1$ Screw location | $z_2$ Screw location | <b>Accessory</b>    |                    |                    |                    |    |    |    |    |
|---------------------|-----------------|---------------------|-----------------|--------------------------|-------|-------|-----|----------------------|----------------------|---------------------|--------------------|--------------------|--------------------|----|----|----|----|
| Aluminum            | Stainless steel | Aluminum            | Stainless steel |                          |       |       |     |                      |                      | GN 911 for Aluminum |                    | GN 911.3 for SST   |                    |    |    |    |    |
|                     |                 |                     |                 |                          |       |       |     |                      |                      | for $z_1$<br>$l_3$  | for $z_2$<br>$l_3$ | for $z_1$<br>$l_3$ | for $z_2$<br>$l_3$ |    |    |    |    |
| B 10                | -               | B 10                | -               | 25                       | 61    | 34,5  | 39  | M6-20                | M6-20                | -                   | -                  | 63                 | -                  | -  | -  | -  |    |
| B 12                | B 12            | B 12                | B 12            | 25                       | 61    | 34,5  | 39  | M6-20                | M6-20                | -                   | -                  | 45                 | 63                 | 45 | 63 | 45 | 63 |
| B 14                | B 14            | B 14                | B 14            | 25                       | 61    | 34,5  | 39  | M6-20                | M6-20                | -                   | -                  | 45                 | 63                 | 45 | 63 | 45 | 63 |
| B 15                | B 15            | B 15                | B 15            | 25                       | 61    | 34,5  | 39  | M6-20                | M6-20                | -                   | -                  | 45                 | 63                 | 45 | 63 | 45 | 63 |
| B 16                | B 16            | B 16                | B 16            | 25                       | 61    | 34,5  | 39  | M6-20                | M6-20                | -                   | -                  | 45                 | 63                 | 45 | 63 | 45 | 63 |
| B 18                | B 18            | B 18                | B 18            | 25                       | 61    | 34,5  | 39  | M6-20                | M6-20                | -                   | -                  | 45                 | 63                 | 45 | 63 | 45 | 63 |
| -                   | B 20            | -                   | B 20            | 25                       | 61    | 34,5  | 39  | M6-20                | M6-20                | -                   | -                  | -                  | -                  | 45 | 63 | 45 | 63 |

**Specification**

- Aluminum
  - Powder coated
  - Black, RAL 9005, textured finish ● **SW**
  - Plain finish, matte shot-blasted ○ **BL**
- Stainless steel AISI CF-8 **NI**
- Matte shot-blasted
- Socket cap screws DIN 912
- Stainless steel AISI 304
- Hex nuts DIN 985
- Stainless steel AISI 304
- Self-locking via polyamide ring
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

**Accessory**

- Adjustable Hand Levers GN 911 / GN 911.3  
→ Page 1784 / 1785

**On request**

- $d_1$  /  $d_2$  with unequal bores

**Information**

The clamping bores of T-angle connector clamps GN 191 are mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw locations  $z_1$  /  $z_2$  the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the adjustable hand levers GN 911 / GN 911.3 listed in the table as accessories.

see also...

- *Construction Tubes GN 990* → Page 1835
- *Retaining Rods / Tubes GN 480.1* → Page 1833
- *T-Angle Linear Actuator Connectors GN 191.1* → Page 1966

|                            |                             |
|----------------------------|-----------------------------|
| How to order (Aluminum)    | <b>1</b> $d_1$              |
|                            | <b>2</b> $d_2$              |
| <b>GN 191-B12-B12-2-SW</b> | <b>3</b> Identification no. |
|                            | <b>4</b> Finish             |

|                                |                             |
|--------------------------------|-----------------------------|
| How to order (Stainless steel) | <b>1</b> $d_1$              |
|                                | <b>2</b> $d_2$              |
| <b>GN 191-B16-B16-2-NI</b>     | <b>3</b> Identification no. |
|                                | <b>4</b> Material           |