



elesa  
Original design MFH

d <sub>1</sub>	Length l		d <sub>2</sub> Bore	d <sub>3</sub>	h
	Nominal dimension	Actual dimension			
9	30	29,5	B 3,5	12	27
10	40	39,5	B 3,5	15	33,5

**Specification**

Plastic, Polyamide (PA)

• Operating temperature -30 °C to +100 °C

• Color

- Black, RAL 9005, matte finish
- Orange, RAL 2004, matte finish
- Gray, RAL 7035, matte finish
- Red, RAL 3000, matte finish
- White, RAL 9002, matte finish

- **SW**
- **OR**
- **GR**
- **RT**
- **WS**

RoHS

Finger handles GN 224.3 with bore hole B 3,5 are intended for fixing with self-tapping screws of thread size ST 4,2 such as DIN ISO 7049 pan head tapping screws.

see also...

	Page
GN 224.1 Finger Handles (Steel)	QVX
GN 224.5 Finger Handles (Stainless Steel)	QVX

**Technical Information**

Strength Properties	QVX
Plastic Characteristics	QVX

How to order

1	d <sub>1</sub>
2	Length l
3	d <sub>2</sub>
4	Color

**GN 224.3-10-40-B3,5-SW**