



**4 Sensitivity**  
 30 Angle minutes,  
 bubble move by 2 mm

2

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	t
17	12	13,2	M 3	13	14,7	5
20	14	13	M 3	14,5	17	5
24	16	15	M 3	17	20	5

**Specification**

**Housing**

- Aluminum
- Anodized, natural color
- Anodized, black

- ALN
- ALS

**Spirit level element**

- Glass plastic body
- Filling
- Colorless-transparent

K

**Casting compound**

Mineral-based

RoHS

**On request**

- Filling, green-transparent
- Other sensitivities
- Housing in brass or stainless steel

Bull's eye spirit levels GN 2280 are used to check the horizontal position of jigs, machines, devices, appliances and instruments.

The mounting threads offset by 120° allow the spirit levels to be aligned in relation to the mounting surface. An alignment ball at the bottom surface of the adjustment plate serves as tilting point. Specific tightening torques of the bolts allow to be achieved, so that the bubble is located inside the marking ring once the horizontal alignment is reached.

**see also...**

	Page
GN 2276 Cross Spirit Levels (for Mounting with Screws)	QVX
GN 2283 Screw-On Spirit Levels (for Mounting with Screws)	QVX
GN 2278 Bull's Eye Spirit Levels (for Insertion into Bore Holes)	QVX
GN 2277 Bull's Eye Spirit Levels (with Mounting Flange)	QVX

**Technical Information**

General Information on Bull's Eye, Screw-On and Cross Spirit Levels	QVX
---	-----

**How to order**

1	Material / Finish
2	d <sub>1</sub>
3	Filling
4	Sensitivity

GN 2280-ALS-20-K-30

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

