



Adjustable hand lever
GN 911 / GN 911.3



- 2 Identification no.**
2 With stainless steel socket cap screw DIN 912



d ₁ Bore	b Swivel width	d ₂	k	l ₁	m	s	t	z Screw location	Accessory Recommended hand lever for z				
									GN 911 for aluminum l ₂	GN 911.3 for stainless steel l ₂			
B 12	B 12	25	6,5	25	64	29,5	10	12,5	M6-20	45	63	-	-
B 14	B 14	25	6,5	25	64	29,5	10	12,5	M6-20	45	63	-	-
B 15	B 15	25	6,5	25	64	29,5	10	12,5	M6-20	45	63	-	-
B 16	B 16	25	6,5	25	64	29,5	10	12,5	M6-20	45	63	-	-
B 18	B 18	25	6,5	25	64	29,5	10	12,5	M6-20	45	63	45	63
-	B 20	25	6,5	25	64	29,5	10	12,5	M6-20	-	-	45	63

Specification

- Aluminum
 - Powder coated Black, RAL 9005, textured finish **● SW**
 - Plain, matte shot-blasted **○ BL**
- Stainless steel AISI CF-8 **NI**
Matte shot-blasted
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
- Stainless Steel Characteristics → Page 2166
- RoHS

Accessory

- Adjustable Hand Levers GN 911 / GN 911.3
→ Page 1784 / 1785



Information

The clamping bore of swivel clamp connectors GN 273 is mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw location z, the socket cap screw reduces the bore cross-section for clamping. For clamping without tools, the socket cap screw can be replaced by an adjustable hand lever GN 911 / GN 911.3 listed in the table as accessory.

Swivel clamp connectors GN 273 can be combined with swivel clamp connectors GN 271, GN 275 or GN 277 to swivel clamp connector joints.

see also...

- Construction Tubes GN 990 → Page 1835
- Retaining Rods / Tubes GN 480.1 → Page 1833
- Swivel Clamp Connector Joints GN 283
(Connection of GN 273 with GN 275) → Page 1765
- Swivel Clamp Linear Actuator Connectors GN 273.1 → Page 1969

How to order (Aluminum)

GN 273-B16-2-SW

1	d ₁
2	Identification no.
3	Finish

How to order (Stainless steel)

GN 273-B20-2-NI

1	d ₁
2	Identification no.
3	Material

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

