



**4 Type**

- C** With thread
- K** With plain hole H7

<b>2</b> $d_1$	<b>3</b> $d_2$ Type C Thread	<b>3</b> $d_3$ H7 Type K Bore	$d_4 \approx$	$h \approx$	$t_1$ min.	$t_2$ min.
16	M 4	B 6	8	15	7	9
20	M 5	B 8	12	18	9	11
25	M 6	B 10	15	22,5	11	14
32	M 8	B 12	18	29	14,5	17
40	M 10	B 16	22	37	18	22
50	M 12*	B 20	27	46	21	28

\* This size is only available in steel and aluminum.

**Specification**

<b>Steel</b> Polished	<b>ST</b>
<b>Aluminum</b> Polished	<b>AL</b>
<b>Stainless Steel</b> AISI 303 Matte shot-blasted	<b>NI</b>
RoHS	

Ball knobs DIN 319 made of steel, aluminum and stainless steel are not on the official DIN standard sheet.

see also...	Page
<b>DIN 319</b> Ball Knobs (Plastic)	QVX

**Technical Information**

ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order

**1** **2** **3** **4**  
**DIN 319-AL-40-M10-C**

<b>1</b>	Material
<b>2</b>	$d_1$
<b>3</b>	$d_2$ ( $d_3$ )
<b>4</b>	Type