

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

Characteristics of the standard executions GN 332		
The tubular handles have the CE marking, low voltage guideline 2014 / 35 / EU		
<b>Emergency stop</b>	2 channel, normally closed contact	
<b>1st button with 2 LED</b>	Changeover contact	
	LED, red and green	
<b>2nd button</b>	Normally open contact	
<b>Contact termination, Pin configuration</b>	Plug M12x1, 12-pole	
<b>Switching voltage / Switching current</b>	max. 24 V DC / max. 0,5 A	
<b>Operating voltage (LEDs)</b>	24 V DC ±15% / 10 mA	
<b>Protection class</b>	Identification no. 1: IP 67 (in screwed condition) Identification no. 2: IP 54	
<b>Button color</b>	for each button a set of caps is included, in this colors: red, green, blue	
Additional variations as special application		
<b>Emergency stop</b>	1 channel	
<b>Number of buttons &gt; 2</b> <b>Button optional with</b>	Normally open contact	
	Normally closed contact	
	Changeover contact	
<b>Button with labelling area</b>		