




Application examples



2 Type

- KS** With cover cap, gliding
- KR** With cover cap, non-gliding



d ₁	d ₂	h ₁	h ₂	h ₃
16	3,2	5	1	3,7
20	4,3	5	1	3,7
25	4,3	5,7	1	4
32	5,3	6,7	1	5

Specification

- Steel
Zinc plated, blue passivated
- Cover caps
 - Type KS:
Polyacetal (POM)
Cream white RAL 9001
 - Type KR:
Elastomer (TPE)
≈ 75 Shore A
Black
- *Plastic Characteristics* → Page 2158
- *Elastomer Characteristics* → Page 2158
- **RoHS**

On request

- Cover cap in other colors

Information

The application examples given above demonstrate the versatility of disks with cover cap GN 338.

Removal of the cover can be done by inserting a screwdriver in the gap on the edge.

How to order

GN 338-25-KS

1 d₁

2 Type

