



4 Type

- KS** With plastic cap, gliding
- KR** With plastic cap, non-gliding

d ₁	d ₂	l ₁		l ₂ ≈	l ₃ ≈	l ₄		A/F	Static load in kN
						Type KS	Type KR		
29	M 6	30	45	8	5	1	0,4	3	6
29	M 8	35	55	8	5	1	0,4	4	13
36	M 8	40	65	9	6	1	0,5	4	13
36	M 10	45	70	9	6	1	0,5	5	18

Specification

- Steel **ST**
 - Property class 5.8
 - Zinc plated, blue passivated
- Hex nut ISO 4035
- Steel zinc plated, blue passivated
- Stainless steel AISI 303 **NI**
 - Hex nut ISO 4035
 - Stainless steel AISI 304
- Plastic caps
 - Type KS
Technopolymer (Polyacetal POM)
White (natural color) RAL 9001
 - Type KR
Elastomer (TPE)
73 shore A ≈
Black
- Strength Values → Page 2152
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

5 Information

Leveling feet GN 339 are used for applications in cases where no jointed link is required between foot and adjusting screw.

For this reason they offer the advantage of reduced height.

The gliding and/or the non-gliding protective cap is safely „fixed“ in the foot.

see also...

- *Disks with Cover Cap GN 338* → Page 1093
- *Insert Bushings GN 448 (for Tubes)* → Page 1498 / 1499
- *Mounts for Leveling Feet GN 349* → Page 1496
- *Ball Jointed Leveling Feet GN 638* → Page 1444

How to order

1	d ₁
2	d ₂
3	l ₁
4	Type
5	Material

GN 339-36-M10-45-KR-ST