



elesa
Original design M.479

2 Type

- A Mounting from the back
- B Mounting from the operator's side

1

$l_1 \pm 0,5$	d_1	d_2	b	h_1	h_2	l_2	l_3	s	t_1	t_2
132	M 8	8,5	23	52,5	13	173	113	9	12	8,5

Specification

Handle

- Plastic, polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black-gray, shiny finish, similar to RAL 7021

Bushing for type A

Brass

Cover cap

Plastic, Polyamide (PA)

- Black-gray, RAL 7021, matte finish
- Orange, RAL 2004, matte finish
- Gray, RAL 7035, matte finish
- Yellow, RAL 1021, matte finish
- Blue, RAL 5024, matte finish
- Red, RAL 3000, matte finish
- Green, RAL 6017, matte finish

- DSG
- DOR
- DGR
- DGB
- DBL
- DRT
- DGN

RoHS

The cover caps of arch handles GN 365 for type A are mounted on the handle, but supplied loose for type B.

Technical Information

Technical Information	Page
Plastic Characteristics	QVX
Strength Properties	QVX

How to order

GN 365-132-A-DSG

1	l_1
2	Type
3	Color of the cover cap