



ROSTFREI
Inox
Stainless
Steel

1 2

Steel

d ₁	Length l					d ₂	d ₃	d ₄	h	k
M 4	10	15	20	30	-	9	12	19	14	8
M 5	10	15	20	25	-	9	12	19	14	8
M 6	10	16	20	25	30	12	14	24	16,5	9,5
M 8	16	20	25	30	40	14	16	30	19,5	11
M 10	20	25	30	40	-	16	18	36	22,5	12,5

1 2

Stainless steel

d ₁	Length l					d ₂	d ₃	d ₄	h	k
M 4	10	15	20	30	-	9	12	19	14	8
M 5	10	15	20	25	-	9	12	19	14	8
M 6	10	16	20	25	30	12	14	24	16,5	9,5
M 8	20	25	30	40	-	14	16	30	19,5	11
M 10	20	25	30	45	55	16	18	36	22,5	12,5

Specification

3

- Plastic
Technopolymer (Polyamide PA)
Black, shiny finish
- Threaded stud
 - Steel —
 - Zinc plated, blue passivated
 - Stainless steel AISI 304 Cu **NI**
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

see also...

- *Knurled Screws GN 591 (Threaded Stud Steel)* → Page 633
- *Knurled Screws GN 421.10 (with Brass / Plastic Pivot)* → Page 638
- *Knurled Screws GN 591.5 (Threaded Stud Stainless Steel)* → Page 635
- *Knurled Screws GN 421 with Loss Protection GN 111.7* → Page 2084

How to order (Steel)

1	d ₁
2	Length l

GN 421-M6-25

How to order (Stainless steel)

1	d ₁
2	Length l
3	Material

GN 421-M6-30-NI