



d <sub>1</sub>			Length l								d <sub>2</sub>	d <sub>3</sub>	h	r	t min.
NI	A4	AL	32	45	55*	64	88*	-	-	M 3	9	26	7	6	
6	-	-	32	45	55*	64	88*	-	-	M 3	9	26	7	6	
8	-	8	55*	64	88*	96	100	120*	128	M 4	12	35	10	8	
10	10	10	88*	100	120*	180*	200	235*	-	M 5	15	43	12	12	
12	-	12	125	160	200	250	-	-	-	M 6	-	51	14	12	
16	-	16	160	200	250	300	-	-	-	M 6	-	59	18	12	

\* suitable for 19" rack and enclosure layout

**Specification**

<b>Stainless steel</b>	<b>NI</b>	
AISI 303 for d <sub>1</sub> = 6, 8, 10		
AISI 304 for d <sub>1</sub> = 12, 16		
• Matte shot-blasted finish	<b>GS</b>	
• Electropolished	<b>EP</b>	
• Location disks for d <sub>1</sub> = 6, 8, 10		
Stainless steel AISI 303		
<b>Stainless steel AISI 316L</b>	<b>A4</b>	
• Matte shot-blasted finish	<b>GS</b>	
• Location disks		
Stainless steel AISI 316L		
<b>Aluminum</b>	<b>AL</b>	
• Powder coated		
- Black, RAL 9005, textured finish	● <b>SW</b>	
- Silver, RAL 9006, textured finish	● <b>SR</b>	
- Red, RAL 3000, textured finish	● <b>RS</b>	
• Anodized, natural color	● <b>EL</b>	
• Location disks for d <sub>1</sub> = 8, 10		
Zinc die casting, nickel plated		

RoHS

Cabinet U-handles GN 425 are manufactured from a bent stainless steel or aluminum profile. Cabinet U-handles with Ø d<sub>1</sub> = 6, 8 and 10 are delivered with two location disks to ensure proper contact of the handle even in the case of large connecting holes. The disks are loosely enclosed.

see also...	<b>Page</b>
<b>GN 425</b> Cabinet U-Handles (Steel)	QVX
<b>GN 425.1</b> Cabinet U-Handles (Aluminum / Stainless Steel, Angled)	QVX
<b>GN 427</b> Cabinet U-Handles (Aluminum, Ellipse Shaped Profile)	QVX

**Technical Information**

Load Rating Information	QVX
Stainless Steel Characteristics	QVX

**Accessory**

<b>GN 181</b> Fastening Sets (Mounting from the Operator's Side)	QVX
--	-----

How to order (Aluminum)

1	Material
2	d <sub>1</sub>
3	Length l
4	Finish

**GN 425-AL-8-88-EL**

How to order (Stainless steel)

1	Material
2	d <sub>1</sub>
3	Length l
4	Finish

**GN 425-A4-10-180-GS**