



1.1

1.2

1.3

1.4

<sup>2</sup> d <sub>1</sub>	<sup>3</sup> Length l	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	r	t min.
20	200	M 8	105	68	22	15
20	300	M 8	105	68	22	15
28	250	M 10	125	78	32	15
28	350	M 10	125	78	32	15
28	500	M 10	125	78	32	15

2.1

2.2

**Specification**

**Aluminum**

- Powder coated
  - Black, RAL 9005, textured finish
  - Silver, RAL 9006, textured finish
- Plain finish, tumbled

RoHS

<sup>1</sup>

<sup>4</sup>

AL

- SW
- SR
- BL

Cabinet U-handles GN 426.1 are manufactured from a bent aluminum profile.

**see also...**

	Page
<b>GN 565.2</b> Inclined Cabinet U-handles (Mounting from the Operator's Side or the Back)	QVX
<b>GN 425.1</b> Cabinet U-Handles (Ø 8, 10, 12 / Aluminum / Stainless Steel, Angled)	QVX
<b>GN 333</b> Tubular Handles (Angled)	QVX

2.3

**Technical Information**

Load Rating Information	QVX
-------------------------	-----

2.4

**Accessory**

<b>GN 181</b> Fastening Sets (Mounting from the Operator's Side)	QVX
--	-----

**How to order**

<sup>1</sup>	<b>Material</b>
<sup>2</sup>	<b>d<sub>1</sub></b>
<sup>3</sup>	<b>Length l</b>
<sup>4</sup>	<b>Finish</b>

**GN 426.1-AL-28-250-SW**

