



EDELSTAHL®
Rostfrei
Inox
Stainless
Steel

² d ₁	³ Length l ±0,5			⁴ h		d ₂	r	t min.
12	125	160	200	75	110	M 6	14	12
16	160	200	300	85	125	M 6	18	12

Specification

- Stainless steel AISI 303 ¹ **NI**
- Matte shot-blasted **GS**
- Powder coated Black, RAL 9005, textured finish **● SW**
- Load Rating Information → Page 2106
- Stainless Steel Characteristics → Page 2166
- RoHS

On request

- Other dimensions
- Other materials
- Other finishes

Information

Cabinet U-handles GN 435, tall design, are made from bent round profiles and are designed for applications requiring more height for gripping. For example, this makes it possible to grab or hold the handle while wearing safety gloves. Some dimensions also satisfy the crane access standard DIN EN 13856.

In addition to serving as a handle, it can also be used as a hose guide, retaining bracket or the like.

see also...

- Cabinet U-Handles GN 425 (Stainless Steel) → Page 147
- Cabinet U-Handles GN 435.3 (Stainless Steel, for Welding) → Page 151
- Cabinet U-Handles GN 426.5 (Stainless Steel) → Page 155
- Cabinet U-Handles GN 426.3 (Steel, for Welding) → Page 157
- Cabinet U-Handles GN 565.5 (Stainless Steel) → Page 108

How to order	
¹ Material	GN 435-NI-12-160-75-SW
² d ₁	
³ Length l	
⁴ h	
⁵ Finish	