



1.1

1.2

1.3

1.4

1

2

d ₁	d ₂	d ₃	h +0,5	k	t min.
22	M 6	13	25	13	12
25	M 8	16	28	14	13
32	M 10	19	32	15	17

2.1

Specification

3

- Plastic
Duroplast (PF)
- Temperature resistant up to 90 °C
- White, RAL 9002, lacquered, shiny **WS**
- Bushing
Stainless steel AISI 303
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

The surface quality of the knurled nut GN 530.1 is of a sufficiently high standard to meet the highest requirements. The flash mark is not visible. Duroplast material is highly resistant to chemicals.

2.2

2.3

2.4

How to order

GN 530.1-25-M8-WS

1	d ₁
2	d ₂
3	Color

