



1.1

1.2

1.3

1.4

1

2

3

d ₁	d ₂	Length l			d ₄	h ₁	h ₂
40	M 8	16	20	25	18	30,5	15
50	M 10	20	25	30	21	34	17
60	M 12	25	30	40	25	39	18

2.1

Specification

- Stainless steel AISI 303
Matte shot-blasted
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

Stainless steel star knobs GN 5335 are a special development intended for the food processing machinery industry. The smooth and enclosed areas as well as the large corner radii comply with the requirements of hygiene standards.

see also...

- *Stainless Steel Star Knobs with Threaded Stud GN 5334* → Page 627
- *Stainless Steel Star Knobs with Threaded Stud GN 5334.4* → Page 627
- *Stainless Steel Wing Screws GN 433* → Page 620
- *Stainless Steel Wing Screws GN 835* → Page 619

2.2

2.3

2.4

How to order

GN 5335-40-M8-20

1	d ₁
2	d ₂
3	Length l

