



<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub>	<b>3</b> Length l	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	t
32	M 5	10, 20, 40	14	26	16	10
32	M 6	10, 20, 40	14	26	16	12
40	M 6	10, 20, 40	16	30	17	12
40	M 8	16, 30, 50	16	30	17	14
50	M 8	16, 30, 50	19	35	19	14
50	M 10	20, 30, 50	19	35	19	16
60	M 10	20, 30, 50	22	41	22	16
60	M 12	20, 30, 50	22	41	22	18

**Specification**

- Plastic  
Technopolymer (Polyamide PA)  
Temperature resistant up to 90 °C
- Colors (shiny finish):  
Black, RAL 9005 **● SW**  
Orange, RAL 2004 **● OR**  
(only version with threaded bushing)
- Bushing  
Brass
- Threaded stud  
Steel zinc plated, blue passivated
- *Plastic Characteristics* → Page 2158
- RoHS



**Information**

Triangular knobs GN 5339 impress by their elegant shape and gleaming color.

How to order (Bushing)

**GN 5339-40-M8-OR**

- 1** d<sub>1</sub>
- 2** d<sub>2</sub>
- 4** Color

How to order (Threaded stud)

**GN 5339-50-M10-30-SW**

- 1** d<sub>1</sub>
- 2** d<sub>2</sub>
- 3** Length l
- 4** Color