



1.1

1.2

1.3

1.4

1

2

3

d ₁	d ₂	Length l	d ₃	h ₁	h ₂
63	M 8	25	23	30,5	16
80	M 10	30	30,5	37	20
100	M 12	40	35	43	23

2.1

Specification

- Plastic Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 130 °C
 - Black, matte finish
- Threaded stud
Steel zinc plated, blue passivated
- Color of the cover cap (matte finish):
 - Black, RAL 9005
 - Orange, RAL 2004
 - Gray, RAL 7035
 - Yellow, RAL 1021
 - Blue, RAL 5024
 - Red, RAL 3000
 - Green, RAL 6017
- Plastic Characteristics → Page QVX
- RoHS

4

Information

The ergonomic shape of the three-lobe knobs with threaded stud GN 533 supports effective gripping, resulting in a high torque.

see also...

- Stainless Steel Three-Lobe Knobs GN 5345 → Page QVX
- Three-Lobe Knobs with Threaded Stud GN 5330 (Plastic) → Page QVX

2.2

2.3

2.4

How to order

1	d ₁
2	d ₂
3	Length l
4	Color of the cover cap

GN 533-100-M12-40-DSW

1

2

3

4

