


Retaining ring rotating,
not removable



4 Loss protection

P With plastic ball chain

d₁	d₂	Length l	d₃	h₁	h₂	h₃	r	t_{min.}
25	M 5	16	12	20	10	2,4	20	10
32	M 6	20	14	23	11,5	2,7	21	10
40	M 8	30	16	27	13,5	3,2	21,5	13
50	M 10	40	19	30	15	3,6	22,5	17

Specification

- Plastic
 - Glass fiber reinforced
 - Temperature resistant up to 60 °C
 - Black, matte finish
- Bushing / threaded stud
Stainless steel AISI 304
- Retaining ring / ball chain
Technopolymer (Polyacetal POM)
- Key ring
Stainless steel
Chemically blackened
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

On request

- With bushing brass
- With threaded stud steel, zinc plated
- Plastic ball chains with other lengths

Information

Three-lobed knobs / knob screws GN 5342.13 can be captively attached to a base element with the help of a ball chain.

The three-lobed knobs are supplied ready **assembled** (with a plastic ball chain).

see also...

- *Star Knobs GN 6336.13 (with Loss Protection)* → Page 551
- *Star Knobs GN 5337.13 (with Loss Protection)* → Page 572
- *Three-Lobed Knobs GN 5342 (Technopolymer, Bushing Stainless Steel)* → Page 594
- *Three-Lobed Knob Screws GN 5342 (Technopolymer, Threaded Stud Stainless Steel)* → Page 595
- *More Star Knobs with Loss Protection GN 111.7* → Page 2084

How to order (Bushing)

1	d ₁
2	d ₂
4	Loss protection

GN 5342.13-40-M8-P

How to order (Threaded stud)

1	d ₁
2	d ₂
3	Length l
4	Loss protection

GN 5342.13-50-M10-40-P