



**3 Type**

- A** Without bore
- E** With threaded blind bore
- D** With threaded through bore
- C** With plain blind bore H7

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Thread Type E / D	<b>2</b> d <sub>3</sub> H7 Bore Type C	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	t <sub>1</sub> min.	t <sub>2</sub>
25	M 5	-	12	16	8	10	11
32	M 6	-	15	21	11	12	13
40	M 6	-	18	26	15	12	13
40	M 8	B 8	18	26	15	15	13
50	M 8	-	21	30	17	15	16
50	M 10	B 10	21	30	17	18	16
60	M 10	-	25	35	18	18	20
60	M 12	B 12	25	35	18	22	20

**Specification**

- **GN 5345**  
Stainless steel AISI 303  
Matte shot-blasted
- **GN 5345.4**  
Stainless steel AISI 316L  
Matte shot-blasted
- *Cross Holes GN 110* → Page 2080
- *ISO Fundamental Tolerances* → Page 2151
- *Stainless Steel Characteristics* → Page 2166
- **RoHS**

**On request**

- Highly polished (PL)  
(only type D and E)

**Information**

Three-lobed knobs GN 5345 / GN 5345.4 have a smooth and sealed surface. They are particularly suitable for use where hygiene requirements are high. Their shape allows relatively high torques to be applied.

see also...

- *Star Knobs DIN 6336 (Stainless Steel)* → Page 540
- *Hand Knobs DIN 6335 (Stainless Steel)* → Page 582
- *Star Knobs GN 5334 (Stainless Steel)* → Page 574
- *Wing Nuts GN 834 (Stainless Steel)* → Page 618

How to order (Stainless steel, AISI 303)	1 d <sub>1</sub>
<b>GN 5345-60-B12-C</b>	2 d <sub>2</sub> (d <sub>2</sub> )
	3 Type

How to order (Stainless steel, AISI 316L)	1 d <sub>1</sub>
<b>GN 5345.4-40-M8-E</b>	2 d <sub>2</sub> (d <sub>3</sub> )
	3 Type