



1.1  
1.2  
1.3  
1.4

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$	$d_3$	$d_4$	$h$	$k$
40	M 8	12	25	10	8,5
40	M 10	13	25	10	8,5

2.1

**Specification**

- Plastic Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 100 °C
  - Black, matte



- Bushing Brass
- *Plastic Characteristics* → Page 2158
- RoHS

**On request**

- Other thread diameters

**Information**

Star nuts GN 567 can be used to lock and secure and require minimal space.

The ergonomic shape makes them easy to grip during use.

see also...

- Flat Knurled Nuts DIN 467 → Page 648

2.2

2.3

2.4

How to order

**GN 567-40-M8-SW**

<sup>1</sup>	$d_1$
<sup>2</sup>	$d_2$
<sup>3</sup>	Color

