



2

d <sub>1</sub>		d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub> ≈	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub> ≈	l <sub>5</sub>	l <sub>6</sub>
GN 598.3	GN 598.5								
18	-	M 5	16	57	15	5	52	9,5	5
21	-	M 5	16	67	15	5	62	9,5	5
22	-	M 5	16	73	15	5	68	9,5	5
23	23	M 6	20	87	19,5	6	80	10,5	7
26	26	M 6	20	102	19,5	6	95	10,5	7
28	28	M 8	26	118	26	10	106	16	10

**Specification**

**Handle**

- Plastic, phenolic resin (PF)
- Operating temperature up to 110 °C
- Black, shiny finish
- Revolving

**GN 598.3**

**Retractable mechanism**

Steel, blackened

**GN 598.5**

**Retractable mechanism**

- Stainless steel
- Spindle, AISI 303
- Flat base, AISI 316LHC sintered

RoHS

1

KU

Retractable handles GN 598.3 / GN 598.5 are used when the handle should not protrude temporarily for space or safety reasons.

see also...

**GN 798.7** Safety Retractable Handles (Retractable Mechanism Steel, Automatic Return to the Retracted Position) QVX

**GN 798.8** Safety Retractable Handles (Retractable Mechanism Stainless Steel, Automatic Return to the Retracted Position) QVX

**Technical Information**

Plastic Characteristics QVX

Stainless Steel Characteristics QVX

How to order (Steel)

**GN 598.3-KU-26**

1 Material

2 d<sub>1</sub>

How to order (Stainless Steel)

**GN 598.5-KU-23**

1 Material

2 d<sub>1</sub>